

Ceramic Glaze Cone Chart and Firing Guide

This quick reference guide shows the cone ranges and recommended firing levels for the ceramic glazes available at Artist Corner. We carry top glaze lines from Amaco, Mayco, and Duncan, supporting low, mid, and high-fire ceramics. **Teachers, schools, and districts are eligible for an exclusive 35% discount on all glaze purchases.**

Glaze Compatibility by Cone Range

Cone Range	Temperature	Glaze Lines
Cone 06 - 04 Low Fire	1828 - 1945°F/ 998 - 1063°C	<ul style="list-style-type: none"> Stroke & Coat Speckled Stroke & Coat Jungle Gems Velvet Underglaze Duncan Envision Foundations Teacher's Palette (TP/TP Light)
Cone 5 - 6 Mid Fire	2167 - 2232°F/ 1186 - 1222°C	<ul style="list-style-type: none"> Potter's Choice Potter's Choice Flux Celadon Satin Matte Stoneware Cosmos Velvet Underglaze Stroke & Coat Speckled Stroke & Coat
Cone 10+ High Fire	2345°F+/ 1285°C	<ul style="list-style-type: none"> Limited compatibility (check manufacturer guidelines) Some stoneware glazes may tolerate Cone 10 with muted results

Helpful Notes

- Always check the manufacturer's specific recommendations for each glaze.
- Cone 5 - 6 firing is the most commonly used range in studio and classroom settings.
- Velvet Underglaze can be fired across a wide range, from Cone 06 to Cone 10.
- Some glazes perform differently in oxidation vs. reduction atmospheres.
- For best layering results, consult manufacturer resources or test combinations.